

Safewell is proud to be an authorised Donaldson Compressed Air & Gas Products Distributor for the Energy and Industrial Sectors.

Safewell is a leader in the life cycle holistic safety management of industrial processes.

Quality of Compressed Air Used for Respiratory Protection in accordance with International Breathing Air Standard BS EN12021:2014 and Medical Pharmacopoeia Breathing Gas Standards. We provide air purification products, air quality testing, safety training and life cycle spares, calibration, servicing and support

Quality of Compressed Air Used in Pharmaceutical / Food Production and Industrial Processes in accordance with ISO 8573-1:2010, Compressed Air Part 1: Contaminants and Purity Classes. We provide air purification products, air quality testing, safety training and life cycle spares, calibration, servicing and support for a range of market sectors

Safety of Automation Systems used on Commercial Dive Support Vessels in accordance with IEC61508 – Functional Safety of Electrical/Electronic/Programmable Electronic Safety-related Systems (E/E/PE, or E/E/PES). Including functional safety audits and design and development of industrial automation systems

This Donaldson CAP Data Sheet is Delivered to you by Safewell

Please contact us today for technical assistance, competitive pricing and excellent customer service: sales@safewell.info

Safewell Solutions Ltd

Brathens Eco Business Park Banchory Aberdeenshire AB31 4BW

T +44 (0) 1330 826 978 **F** +44 (0) 1330 825 308 **E** sales@safewell.info **W** www.safewell.info



HEATLESS REGENERATED ADSORPTION DRYERS ULTRAPAC 2000



Adsorption Drying – why?

Compressed air is an important process and energy medium applied in almost all areas of industrial production. The atmospheric air taken in contains contaminants, dirt particles and humidity, i.e. water vapour which condensates in compressed air pipes. This condensation can lead to considerable costs (corrosion, freezing etc.). These costs can be avoided by the application of an Ultrapac 2000 dryer. This complete Ultrapac purification system includes a prefilter with automatic condensate drain, adsorption dryer and afterfilter.

The prefilter retains solids and condensate (oil/water mixture) up to a residual oil content of 0.03 mg/m³. The adsorption dryer next in line adsorbs the moisture in the compressed air up to a pressure dew-point of -40 °C.


Finally, in the afterfilter, remaining particles from the drying agent are retained.



Two Ultrapac 2000 dryers installed in a bottling plant

Adsorption Dryer Ultrapac 2000

- 1 Dryer inlet
- 2 Prefilter
- 3 Condensate drain
- 4 Multifunction unit
- 5 Drying agent cartridge
- 6 Afterfilter
- 7 Dryer outlet
- 8 Processor control



Ultrapac 2000: The all-round Talent with versatile Applications

- Laser-cutting systems
- Bottling plants
- Dental laboratories
- Packaging machines
- Rail vehicles
- Optical measuring systems
- Sprinkler systems

Security in every Detail

Ultrapac 2000

Ultrapac 2000 Superplus – Quality and Safety

- Complete purification system including prefilter, afterfilter and electronic condensate drain, all components factory-assembled, minimum installation requirements.
- Drying agent in cartridges, easier service conditions, no complicated snow filling of the drying agent.
- Unique multifunction block including all mechanical and electronical components.
- Exceptionally compact, space saving design, minimum space requirements for installation.
- In case of central application, the system can be connected to a compressor in order to save regeneration air.



Control system – Ultrapac 2000 Superplus. Clear text display of the current operational status. Indication of the optimum and most efficient time for exchanging the drying agent cartridge. Output signal for remote monitoring.

Drying Agent Cartridge – the superior Solution:


Fixed drying agent – thus minimum drying agent abrasion and long service life. Reduced storage, logistics and drying agent exchange requirements.



Ultrapac 2000 Superplus:


The intelligent System Solution

- Load dependant control for adsorption of cycle times to the actual water load with varying inlet conditions; regeneration air can thus be saved.
- Unique self-monitoring system: the regeneration air flow rate is continuously measured and all deviations from set-points are detected at an early stage.
- Text display indicating malfunctions, service conditions and status. Available in more than 10 languages.
- Communication port for programming. Communication port for transmitting service and alarm messages.
- Economizer for determination of the optimum time for a filter element exchange.



Technical Data Ultrapac 2000

Type		Volume dimensions flow* Inlet	Compressed air consumption*	Connection	Condensate connection	Dimensions		
						Width (A)	Height (C)	Depth (B)
		m³/h	m³/h	G	mm	mm	mm	mm
Mini	0005	5	0.85	1/2	6	300	343	121
	0010	10	1.70	1/2	6	300	591	121
	0015	15	2.55	1/2	6	300	853	121
	0025	25	4.25	1/2	6	300	1377	121
Midi	0035	35	5.95	1	6	531	665	195
	0050	50	8.50	1	6	531	917	195
	0065	65	11.05	1	6	531	1169	195
	0080	80	13.60	1	6	531	1421	195
	0100	100	17.00	1	6	531	1673	195



Explanation: *related to the intake of the compressor +20 °C, 1 bar abs., at a compressed air inlet temperature of +35 °C and 7 bar g operating pressure.

Pressure dewpoint: -40 °C Minimum pressure: 4 bar g. Maximum pressure: 16 bar g. Inlet temperature: min. +5 °C, max. +50 °C (dimensioning see below).

Sizing

f	4 bar (g)	5 bar (g)	6 bar (g)	7 bar (g)	8 bar (g)	9 bar (g)	10 bar (g)	11 bar (g)	12 bar (g)	13 bar (g)	14 bar (g)	15 bar (g)	16 bar (g)
25 °C	0.69	0.82	0.96	1.10	1.24	1.38	1.50	1.50	1.50	1.50	1.50	1.50	1.50
30 °C	0.69	0.82	0.96	1.10	1.24	1.38	1.50	1.50	1.50	1.50	1.50	1.50	1.50
35 °C	0.63	0.75	0.88	1.00	1.13	1.26	1.38	1.50	1.50	1.50	1.50	1.50	1.50
40 °C	0.48	0.58	0.68	0.77	0.87	0.96	1.06	1.16	1.25	1.35	1.45	1.50	1.50
45 °C	0.38	0.45	0.53	0.60	0.68	0.75	0.83	0.90	0.98	1.05	1.13	1.20	1.28
50 °C	0.30	0.36	0.42	0.48	0.54	0.60	0.66	0.72	0.78	0.84	0.90	0.96	1.02

$\dot{V}_{corr} = \frac{\dot{V}_{nom}}{f}$ Example: $\dot{V}_{nom} = 22 \text{ m}^3/\text{h}$, Inlet temperature = 30 °C, Operating pressure = 10 bar (g)

$\dot{V}_{corr} = 22 \text{ Nm}^3/\text{h} = 14,66 \text{ Nm}^3/\text{h}$

1,50 Calculated dryer size: **Ultrapac 2000, Type 0015**

Donaldson
Ultrafilter

Compressed Air Filtration · Filters for Sterile Air, Steam and Liquids · Refrigerant Drying · Adsorption Drying · Condensate Drains · Condensate Purification Systems · Process Air and Gas Processing



Donaldson
FILTRATION SOLUTIONS

Total Filtration Management

Donaldson offers a wide variety of solutions to reduce your energy costs, improve your productivity, guarantee production quality and help protect the environment.

Total Filtration Service

A comprehensive range of services especially designed to keep your production at peak performance and at the lowest total cost of ownership.

Please contact us:

Donaldson Europe B.V.B.A.

Research Park Building No. 1303 · Interleuvenlaan 1

B-3001 Leuven · Belgium

Phone +32(0)16 38 38 11 · Fax +32(0)16 40 00 77

CAP-europe@donaldson.com · www.donaldson.com